




prisaa



.....affordable TOFD and PA at your fingertips.




PA

As Simple as you want

- 30 Second Configuration
- Single Hand Operation
- Interactive Help & 3D views
- Configuration & Calibration Wizards
- “Parameter Genius” for additional guidance
- Minimize training: Common User Interface

As Capable as you need

- UT, TOFD & PA Inspection Modes
- Unique cursors for precision measurement
- Recordability: screen shots, full data recording, fully traceable.
- UT Studio - Fast and dynamic reporting
- Customized imaging layout.... over 25 to choose from.



TOFD

STEP UP from conventional UT to phased array.

- Formats available are:
- Prisma UT
 - Prisma UT + TOFD
 - Prisma UT + PA
 - Prisma UT + PA + TOFD

Upgradeable anytime, anywhere!

UT

STEP UP



prisma series

.....true performance to meet all your inspection requirements.



The **prisma** is the latest product from Sonatest's technician focused product development and research. An advanced ultrasonic flaw detector offering the technician an extremely comprehensive tool for test and measurement, which can be upgraded to include TOFD and Phased Array capability. An upgrade can be carried out wherever you are, there is no need to return the instrument, eliminating any downtime.

Simple controls, superior performance, advanced features and a rugged enclosure deliver simplicity, capability and reliability to the technician's finger tips.

With the best display size and resolution in its category, the **prisma** provides the end user with an intuitive and workflow driven interface, excellent imaging capability uses the Full screen mode allowing 100% of the display to be used for Scan Imaging. Numerous palettes are accessible for all scan types "see things how you want to", in amplitude or depth C-Scans, customise your palettes. Take full advantage of the advanced display modes which include smoothing, contouring and averaging all available to enhance your signal quality.

The **prisma** is constructed to exacting standards using a rigid, shock mounted, internal chassis surrounded by an impact absorbing enclosure and sealed to IP66; which ensures the unit is fully sealed against fine dust and jets of water.

Typical applications are broad but include Weld Inspection, Corrosion Mapping, Aerospace and Composite Testing.

Prisma UT

The Prisma UT model is fully loaded, carrying all the basic and advanced features of the Sonatest flaw detector range. Prisma UT offers damping control to either optimize near surface resolution or energy transmission. The ability to capture screens is standard combined with automatic reporting capability which enables reports to be formatted with relative bespoke customer information such as logos etc. The most popular flaw sizing techniques such as DAC, AVG/DGS, TGC and AWS are all on-board.

Thanks to the on-board software enhancing the B and C-Scan imaging capabilities, the Prisma UT enables field technicians to conduct dedicated corrosion and composite inspections, together with comprehensive on-site thickness profiling.

Prisma TOFD

Ultrasonic Time of Flight Diffraction (TOFD) has gained in popularity over the last decade and via the Prisma TOFD, Sonatest brings to the market a truly portable and powerful TOFD unit. Knowing that TOFD inspection can be carried out on wall thickness as thin as 6mm (1/4"), the Prisma offers the best digitizing frequency of its category going up to 200MHz. Simply put this means that high frequency transducers can be used, ensuring the most accurate flaw height sizing possible.

TOFD is a versatile technique; with two UT channels the Prisma permits the inspection of thick component in a single pass. This is enhanced by the high voltage square wave pulsers delivering up to 450V.

Prisma TOFD offers the complete hardware configuration to deliver the best performance, but it would be incomplete without the on-board software features such as hyperbolic cursors, lateral wave straightening and lateral wave removal. S, True Top, Side and End view extractions, together with C-Scans, are all supported.

Prisma PA

Ultrasonic Phased Array technology has become the established method for advanced NDT testing applications. Phased Array Techniques allow the user to cover a wider volume of inspection; such as being able to cover the complete span of a weld without the need to move or reposition the transducer. This is possible due to phased array enabling beams to be electronically steered. This technique results in comprehensive imaging of the results showing a quasi cross section of the inspected part.

With the Prisma PA you can switch easily and quickly between the UT and PA operating modes with a simple press of a button, no data or time is lost.

The Inspection Plan shows the operator in 2D and 3D where probes are positioned on the test part, simplifying the inspection set up and providing an inspection reference for reporting. All adjustments to focal laws are instantaneous. Multiple sectorial scans, true top, side and end view extractions, together with C-Scans, are all supported.

UT Studio

UT Studio is a PC based software, which accompanies the Prisma and enables powerful post analysis capability. Not only does it offer excellent report generation features but new views can be generated and comparative analysis can be conducted by opening multiple inspection data files, re-gating and producing fully illustrated reports. Working in a familiar "drag and drop" environment the end user can create multiple views such a Top, End and B-Scan visual files by simply dragging Prisma data files onto templates for presentations.



Full recordability of data when using the Prisma is standard, which means that screenshots and all data can be retained and analyzed at a later date using UT Studio. IN using the full data gathering capability - traceability can be achieved; hence repeatability of the inspection and results can be confirmed.

Powerful measurement cursors and extractors can be added to identify indications, size and annotate defects. Reports are easily generated and can be exported into PDF format for review and circulation.

Free downloads of UT Studio Viewer are available for the technician's client to use.

	Conventional UT	Phased Array
Pulsers		
Configuration	2 UT Channels	16:16 or 16:64
Test Mode	Pulse-Echo, Transmit/Receive and TOFD	Pulse-Echo, Transmit/Receive
Transducer Socket	LEMO 1 or BNC	I-PEX
Pulse Voltage	-100 V to -450 V (in steps of 10 V)	-25 V to - 75 V (in steps of 5 V)
Pulsar	Pulse width adjustable from Spike to 2000ns (2.5ns resolution)	Pulse width adjustable Spike to 1000ns (2.5ns resolution)
PRF	3 Hz to 5 kHz	3 Hz to 5 kHz
Pulse Shape	Negative Square Wave (with ActiveEdge)	Negative Square Wave (with ActiveEdge)
Pulse Width	Adjustable: 25ns to 2000ns (2.5 ns resolution)	Adjustable: 25ns to 1000ns (2.5 ns resolution)
Edge Time	15 ns in 50 Ω load @200 V	12 ns in 50 Ω load @50 V
Output Impedance	5 Ω	<10 Ω
Synchronisation	Encoder or free-running (time based)	Encoder or free-running (time based)
Focus Delay Range	n/a	0 to 10 μs (2.5 ns resolution)
Damping Resistor	Selectable: 50 Ω or 400 Ω	n/a
Receivers		
Gain Range	120 dB (-40 dB to 80 dB), Analogue Gain	0 to 80 dB (0.1 dB steps), Analogue Gain
Max Input Voltage	25 Vp-p	200 mVp-p
Input Impedance	1 kΩ (pitch and catch)	200 Ω
Bandwidth	200 kHz to 22 MHz (-3 dB)	200 kHz to 14 MHz
Analog Filters	4	3
Digital Filters	10	10
Rectification	Full wave, positive, negative, none (RF)	Full wave, positive, negative, none (RF)
Single Enhancement	Digital filters, Averaging, Smoothing, Contouring	Digital filters, Smoothing
Focus Delay Range	n/a	0 to 10ns (16 ns resolution interpolated to 3.8 ns)
Data Acquisition		
Architecture	2 channels, true 200 MHz sampling rate	16 Channels, Full digital Delay & Sum
Digitizer Resolution	12 bit ADC	12 bit ADC
Amplitude Measurement	[0% to 100%] or [0% to 150%] FSH	[0% to 100%] or [0% to 150%] FSH
Data Processing	16 bits/sample	16 bits/sample
Data Recording	Full raw data recording	Full raw data recording
File Size	up to 3 GB	up to 3 GB
Digitizing Frequency	50 MHz, 100 MHz, 200 MHz	65 MHz
Focal Laws	n/a	128
Focussing Type	n/a	Constant Depth, Constant Path, Constant Offset
Max A-Scan Length	8192 samples	4096 samples
Sub-Sampling	1:1 to 1:128	1:1 to 1:128
Reference	Initial Pulse or Gate/IFT supported	Initial Pulse or Gate/IFT supported
Trigger Sync.	Encoder or Internal	Encoder or Internal
Scan & Views		
Supported Scans	A-Scan & TOFD	S-Scan or L-Scan
Number of Scans	up to 4	1 (with up to 4 extracted A-Scans)
Views	A, B, C-Scan plus TOFD	A, B, C, L, S-Scan plus End & Top view
Colour Maps	up to 10	up to 10
Number of Layouts	12	17
Cursors		
Cursor Types	Cartesian, Hyperbolic (TOFD)	Cartesian, Extraction Box, Angular
Measurements	Path Length, Depth, Surface Distance, DAC, AWS, DGS	Path Length, Depth, Surface Distance, DAC, AWS

	Conventional UT	Phased Array
DAC & TCG		
DAC points	16	16
DAC	1 with 3 "sub DACs"	1 with 3 "sub DACs" per focal Law
TCG points	16	16
Gain Range	60 dB	40 dB
Max Gain Slope	60 dB/μs	50 dB/μs
Gates		
A-Scan Gates	4 gates per A-Scan	4 gates per A-Scan (3 extracted A-Scans per S/L-Scan)
Gate Trigger	Flank/Peak	Flank/Peak
S/L-Scan	n/a	1 Extraction Box
Alarm LED	1 (sync on all gates & DACs)	1 (sync on all gates & DACs)
Measurements (A-Scan)	Peak & Flank (FSH, dB, D, BPL, SD) and Echo-to-Echo	Peak & Flank (FSH, dB, D, BPL, SD) and Echo-to-Echo
Interface & Reporting		
Help System	Active parameter description and Optimization Tips	
Configuration Validation	Dynamic Help with Parameter Genius	
Wizards	Configuration, Velocity and Zero, Wedge Delay, Sensitivity, TCG, DAC, DGS, Element Activation, Encoder	
Languages (dynamic)	English, German, French, Spanish, Russian, Chinese	
Report Generation	PDF File (includes scans, setup, measurements, etc.), PNG screen capture, Customer Logo	
PDF Reader	Allows viewing any uploaded PDF file	
Inputs & Outputs		
Encoder	1 or 2 axis encoding (quadrature input)	
Digital Inputs	2 input lines (5V TTL)	
Digital Outputs	2 Output lines (5V TTL, 20 mA) for alarm or other external control	
Analogue Outputs	2 Analogue Output lines (0-2V)	
Power Output	5V, 350 mA, current limited	
Enclosure		
Dimensions (HxWxD)	205mm x 300mm x 90 mm	
Weight	3.5 kg (with battery)	
Display Size	8.4 inch (diagonal)	
Display Resolution	800 x 600	
Display Colours	260k (65535 colours for scan palettes)	
Display Type	TFT LCD, 450 Cd/m2, with 2% reflectivity	
USB ports	3 USB Master ports	
Ethernet	100 Mbps	
Battery & Power Supply		
Battery Type	Intelligent Li-ion	
Number of batteries	1	
Operation	On battery or on External power (DC Power Pack)	
Battery Replacement	Yes, no tools required	
Battery Recharge	Recharge in unit (with unit On or OFF) - External Battery Charger (std)	
Battery Life	Typical: 7 hours in UT mode, 6 hours in PA mode	
Environmental		
IP Rating	Designed to meet IP66	
Operating Temperature	-10 °C to 45 °C (14 °F to 113 °F)	
Storage Temperature	-25°C to 60°C (-13°F to 140°F)	

prisma

prisma UT Standard Kit

Dual UT Channels with:

- A-Scan Recording
- 2 Axis Encoding
- Interface Triggering (IFT)

A,B and C Scan Displays

USB Stick (8GB)

Couplant

User Manual/ Quick User Guide

2 Point Neck Harness

Lithium-Ion Battery Packs (x2)

External battery charger

Power Cord & Power Supply adaptor

Screen Protector (Anti-Glare)

Transport Case (Airplane Carry on Size)

prisma UT/PA 16/16 Standard Kit

Dual UT channel kit above plus

16:16, manual PA

Options

UT option

TOFD

*encoding for UT is standard

*IFT for UT is standard

PA option

16:64

2 axis encoding & recording for PA

IFT for PA

Encoder Y-Splitter

Distributed by:

SONATEST LTD

Dickens Road, Old Wolverton, Milton Keynes, MK12 5QQ, UK.

Tel: +44 (0)1908 316345 Fax: +44 (0)1908 321323

www.sonatest.com sales@sonatest.com

SONATEST INC

12775 Cogburn, San Antonio, TX 78249, USA

Tel: +44 (0)1908 316345 Fax: +44 (0)1908 321323

www.sonatest.com sales@sonatestinc.com



Cert No: Q5036

